



# MASTER PL-C 2 Pin

## MASTER PL-C 26W/827/2P 1CT/5X10CC

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G24D-3 [G24d-3]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,800 lumen
Color Designation	Incandescent White
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	68 lm/W
Color rendering index (CRI)	82


Operating and Electrical	
Power Consumption	26.5 W
Lamp Current (Nom)	0.335 A
Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	32 kWh

MASTER PL-C 2 Pin

Product Data	
Full product code	692341076113900
Order product name	MASTER PL-C 26W/827/2P 1CT/5X10CC
Order code	927906182705
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50


Material Nr. (12NC)	927906182705
Full product name	MASTER PL-C 26W/827/2P 1CT/5X10CC
EAN/UPC - Case	6923410762174
EAN/UPC - Product/Case	6923410761139

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/827/2P 1CT/ 5X10CC	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 26W/827/2P 1CT/5X10CC

Lifetime




Life Expectancy Diagram - MASTER PL-C 26W/827/2P 1CT/5X10CC



Life Expectancy Diagram - MASTER PL-C 26W/827/2P 1CT/5X10CC

MASTER PL-C 2 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 26W/827/2P 1CT/5X10CC

