



PL-C consumer products

PL-C 26W/840/2P 1BC/6

The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base. Not suitable for dimming.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	G24D-3 [G24d-3]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	1,800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	68 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	26.5 W
Lamp Current (Nom)	0.335 A
Controls and Dimming	
Dimmable	No

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	32 kWh
Product Data	
Order product name	PL-C 26W/840/2P 1BC/6
Full product name	PL-C 26W/840/2P 1BC/6
Full product code	871829116712900
Order code	927906184016
Material Nr. (12NC)	927906184016
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291167129
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291167136


PL-C consumer products

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 26W/840/2P 1BC/6	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

Photometric data




Spectral Power Distribution Colour - PL-C 26W/840/2P 1BC/6

Lifetime




Life Expectancy Diagram - PL-C 26W/840/2P 1BC/6



Life Expectancy Diagram - PL-C 26W/840/2P 1BC/6

Lifetime



Lumen Maintenance Diagram - PL-C 26W/840/2P 1BC/6

