



MASTER PL-C 2 Pin



MASTER PL-C 26W/840/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G24D-3 [G24d-3]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	10,000 h
Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	1,800 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	68 lm/W
Colour rendering index (CRI)	80

Operating and Electrical	
Power Consumption	26.5 W
Lamp current (nom.)	0.335 A
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	27 kWh
EPREL registration number	423288


Product Data	
Order product name	MASTER PL-C 26W/840/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Full product name	MASTER PL-C 26W/840/2P 1CT/5X10BOX
Full EOC	871150062100970
Order code	62100970
Material no. (12 NC)	927906184040
Local order code	26PLC8402PIN
SAP numerator – quantity per pack	1


EAN/UPC – Product/Case	8711500621009
Numerator – packs per outer box	50
EAN/UPC – Case	8711500715968

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/840/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 26W/840/2P 1CT/5X10BOX

Lifetime



Life Expectancy Diagram - MASTER PL-C 26W/840/2P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 26W/840/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 26W/840/2P 1CT/5X10BOX

