



# PL-T Triple 4-Pin Base Energy Advantage

## PL-T 32W/830/XEW/A/4P/ALTO 27W

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


### Product data

General Information	
Cap-Base	GX24Q-3 [GX24q-3]
Features	ALTO® (ALTO)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,900 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	70 lm/W
Color rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	28 W
Lamp Current (Nom)	0.320 A

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-T 32W/830/XEW/A/4P/ALTO 27W
Full product name	PL-T 32W/830/XEW/A/4P/ALTO 27W
Order code	220210
Material Nr. (12NC)	927906983020
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677220211
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677220216


# PL-T Triple 4-Pin Base Energy Advantage

## Dimensional drawing



Product	D (max)	B (max)	C (max)
PL-T 32W/830/XEW/A/4P/ALTO 27W	41.0 mm	123.0 mm	138.7 mm

## Photometric data



Spectral Power Distribution Colour - PL-T 32W/830/XEW/A/4P/ALTO 27W

