



MASTER PL-C 4 针

MASTER PL-C 10W/840/4P 1CT/5X10BOX

紧凑型节能荧光灯。紧凑的长弧结构，低压低汞荧光灯管。由 4 根平行的细荧光灯管组成

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般信息	
底盖	G24Q-1 [G24q-1]
灯技术	
颜色代码	840 [CCT of 4000K]
光通量	600 lm
颜色名称	冷白色 (CW)
相关色温 (标称)	4000 K
光效 (额定)(标称)	60 lm/W
显色指数 (CRI)	82
操作和电气	
功耗	10.0 W
灯具电流 (标称)	0.190 A
控制和调光	
可调光	是

审批和申请	
汞 (Hg) 含量 (标称)	1.4 mg
能耗 kWh/1000 h	11 kWh
产品数据	
订单产品名称	MASTER PL-C 10W/840/4P 1CT/5X10BOX
完整的产品名称	MASTER PL-C 10W/840/4P 1CT/5X10BOX
完整产品代码	692341076119100
订购代码	927907084005
材料编号 (12NC)	927907084005
计算器 - 每包数量	1
EAN/UPC - 产品/箱	6923410761191
计算器 - 每个外包装箱中的包数	50
EAN/UPC - 案例	6923410762235


MASTER PL-C 4 针

二维绘图




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 10W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	109.9 mm

光度数据




Spectral Power Distribution Colour - MASTER PL-C 10W/840/4P 1CT/5X10BOX

寿命




Life Expectancy Diagram - MASTER PL-C 10W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 10W/840/4P 1CT/5X10BOX

MASTER PL-C 4 针

寿命



Lumen Maintenance Diagram - MASTER PL-C 10W/840/4P 1CT/5X10BOX

