



MASTER PL-C 4 Pin

MASTER PL-C 10W/840/4P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	G24Q-1 [G24q-1]	80	
Flux measurement reference	Sphere		
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power Consumption	10.4 W
Luminous Flux	600 lm	Lamp Current (Nom)	0.190 A
Color Designation	Cool White (CW)	Controls and Dimming	
Chromaticity Coordinate X (Nom)	0.38	Dimmable	Yes
Chromaticity Coordinate Y (Nom)	0.38	Approval and Application	
Correlated Color Temperature (Nom)	4000 K	Energy Efficiency Class	G
Luminous Efficacy (rated) (Nom)	60 lm/W	Mercury (Hg) Content (Max)	1.4 mg
		Mercury (Hg) Content (Nom)	1.4 mg

MASTER PL-C 4 Pin


Energy Consumption kWh/1000 h	11 kWh
EPREL Registration Number	423297

Product Data

Order product name	MASTER PL-C 10W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-C 10W/840/4P 1CT/5X10BOX
Full product code	871150062330070
Order code	62330070


Material Nr. (12NC)	927907084040
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500623300
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500711038

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 10W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	109.9 mm



Photometric data




Spectral Power Distribution Colour - MASTER PL-C 10W/840/4P 1CT/5X10BOX

MASTER PL-C 4 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C 10W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 10W/840/4P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-C 10W/840/4P 1CT/5X10BOX

