



MASTER PL-C 4 Pin

MASTER PL-C 13W/865/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|------------------------------------|--------------------|
| Cap-Base | G24Q-1 [G24q-1] |
| Light Technical | |
| Color Code | 865 [CCT of 6500K] |
| Luminous Flux | 845 lm |
| Color Designation | Cool Daylight |
| Correlated Color Temperature (Nom) | 6500 K |
| Luminous Efficacy (rated) (Nom) | 63 lm/W |
| Color rendering index (CRI) | 80 |


| Operating and Electrical | |
|-------------------------------|---------|
| Power Consumption | 13.0 W |
| Lamp Current (Nom) | 0.170 A |
| Controls and Dimming | |
| Dimmable | Yes |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 1.4 mg |
| Energy Consumption kWh/1000 h | 15 kWh |

MASTER PL-C 4 Pin

| Product Data | |
|---------------------|------------------------------------|
| Order product name | MASTER PL-C 13W/865/4P 1CT/5X10BOX |
| Full product name | MASTER PL-C 13W/865/4P 1CT/5X10BOX |
| Full product code | 871150027703900 |
| Order code | 927907186501 |
| Material Nr. (12NC) | 927907186501 |


| | |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500277039 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8711500277114 |

Dimensional drawing




| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|--|---------|----------|---------|----------|----------|
| MASTER PL-C 13W/865/4P 1CT/ 5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 131.9 mm |

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 13W/865/4P 1CT/5X10BOX

Lifetime



Life Expectancy Diagram - MASTER PL-C 13W/865/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 13W/865/4P 1CT/5X10BOX

MASTER PL-C 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 13W/865/4P 1CT/5X10BOX

