



# MASTER PL-C 4 Pin



## MASTER PL-C 18W/840/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Lamp current (nom.)	
Cap base	G24Q-2 [G24q-2]	0.230 A	
Flux measurement reference	Sphere	Controls and Dimming	
<b>Light Technical</b>		Dimmable	Yes
Colour Code	840 [CCT of 4000K]	Approval and Application	
Luminous Flux	1,200 lm	Energy Efficiency Class	G
Colour designation	Cool White (CW)	Mercury (Hg) content (max.)	1.4 mg
Chromaticity Coordinate X (Nom)	0.38	Mercury (Hg) content (nom.)	1.4 mg
Chromaticity Coordinate Y (Nom)	0.38	Energy consumption kWh/1,000 hours	19 kWh
Correlated Colour Temperature	4000 K	EPREL registration number	423303
Luminous efficacy (rated) (nom.)	67 lm/W	Product Data	
Colour rendering index (CRI)	80	Order product name	MASTER PL-C 18W/840/4P 1CT/5X10BOX
Operating and Electrical		Full product name	MASTER PL-C 18W/840/4P 1CT/5X10BOX
Power Consumption	18.4 W	Full EOC	871150062334870
		Order code	62334870

# MASTER PL-C 4 Pin

Material no. (12 NC)	927907284040
Local order code	18PLC8404PIN
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500623348


Numerator – packs per outer box	50
EAN/UPC – Case	8711500715906

## Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 18W/840/4P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm

## Photometric data




Spectral Power Distribution Colour - MASTER PL-C 18W/840/4P 1CT/5X10BOX

## Lifetime



Life Expectancy Diagram - MASTER PL-C 18W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 18W/840/4P 1CT/5X10BOX

# MASTER PL-C 4 Pin

## Lifetime



Lumen Maintenance Diagram - MASTER PL-C 18W/840/4P 1CT/5X10BOX

