



# MASTER PL-C 4 Pin

## MASTER PL-C 18W/865/4P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


|                     |        |                               |                                    |         |
|---------------------|--------|-------------------------------|------------------------------------|---------|
| General Information |        | Lamp Current (Nom)            |                                    | 0.230 A |
| Cap-Base            | G24q-2 |                               |                                    |         |
| Light Technical     |        | Controls and Dimming          |                                    |         |
|                     |        | Dimmable                      | Yes                                |         |
|                     |        | Approval and Application      |                                    |         |
|                     |        | Mercury (Hg) Content (Nom)    | 1.4 mg                             |         |
|                     |        | Energy Consumption kWh/1000 h | 20 kWh                             |         |
|                     |        | Product Data                  |                                    |         |
|                     |        | Order product name            | MASTER PL-C 18W/865/4P 1CT/5X10BOX |         |
|                     |        | Full product name             | MASTER PL-C 18W/865/4P 1CT/5X10BOX |         |
|                     |        | Full product code             | 871150027704600                    |         |

MASTER PL-C 4 Pin

|                               |               |
|-------------------------------|---------------|
| Order code                    | 927907286501  |
| Material Nr. (12NC)           | 927907286501  |
| Numerator - Quantity Per Pack | 1             |
| EAN/UPC - Product/Case        | 8711500277046 |


|                                 |               |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 50            |
| EAN/UPC - Case                  | 8711500277121 |

Dimensional drawing




| Product                                | D (max) | D1 (max) | A (max)  | B (max)  | C (max)  |
|--|---------|----------|----------|----------|----------|
| MASTER PL-C 18W/865/4P 1CT/<br>5X10BOX | 27.1 mm | 27.1 mm  | 109.5 mm | 128.0 mm | 142.9 mm |

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 18W/865/4P 1CT/5X10BOX

Lifetime




Life Expectancy Diagram - MASTER PL-C 18W/865/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 18W/865/4P 1CT/5X10BOX

MASTER PL-C 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 18W/865/4P 1CT/5X10BOX

