



MASTER PL-C 4 Pin

MASTER PL-C 18W/865/4P 1CT/5X10CC

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G24Q-2 [G24q-2]
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	1,120 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	62.3 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	18.0 W

Lamp Current (Nom)	0.230 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	20 kWh
Product Data	
Order product name	MASTER PL-C 18W/865/4P 1CT/5X10CC
Full product name	MASTER PL-C 18W/865/4P 1CT/5X10CC
Full product code	692341076128300

MASTER PL-C 4 Pin


Order code	927907286505
Material Nr. (12NC)	927907286505
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923410761283

Numerator - Packs per outer box	50
EAN/UPC - Case	6923410762327

Dimensional drawing


Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 18W/865/4P 1CT/ 5X10CC	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-C 18W/865/4P 1CT/5X10CC

Lifetime




Life Expectancy Diagram - MASTER PL-C 18W/865/4P 1CT/5X10CC

Life Expectancy Diagram - MASTER PL-C 18W/865/4P 1CT/5X10CC

MASTER PL-C 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 18W/865/4P 1CT/5X10CC

