



PL-L Long 4-Pin Base

PL-L 40W/830/4P/RS/IS 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	2G11
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	3,500 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	87 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	36.3 W
Lamp Current (Nom)	0.320 A
Voltage (Nom)	126 V

Voltage (Nom)	126 V
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	PL-L 40W/830/4P/RS/IS 1CT/25
Full product name	PL-L 40W/830/4P/RS/IS 1CT/25
Order code	300426
Material Nr. (12NC)	927908008329
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677111786
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677111781


PL-L Long 4-Pin Base

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-L 40W/830/4P/RS/IS 1CT/25	1-9/16 inch	3/4 inch	21-1/4 inch	22-1/4 inch	22-1/2 inch

Photometric data



Spectral Power Distribution Colour - PL-L 40W/830/4P/RS/IS 1CT/25

