



PL-T Triple 4-Pin Base Energy Advantage

PL-T 42W/841/XEW/A/4P/ALTO 33W

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

| General Information | | Controls and Dimming | |
|------------------------------------|--------------------|---------------------------------|--------------------------------|
| Cap-Base | GX24Q-4 [GX24q-4] | Dimmable | Yes |
| Features | ALTO® (ALTO) | | |
| Light Technical | | Approval and Application | |
| Color Code | 840 [CCT of 4000K] | Mercury (Hg) Content (Nom) | 1.4 mg |
| Luminous Flux | 2,300 lm | | |
| Color Designation | Cool White (CW) | Product Data | |
| Correlated Color Temperature (Nom) | 4100 K | Order product name | PL-T 42W/841/XEW/A/4P/ALTO 33W |
| Luminous Efficacy (rated) (Nom) | 67 lm/W | Full product name | PL-T 42W/841/XEW/A/4P/ALTO 33W |
| Color rendering index (CRI) | 82 | Order code | 220293 |
| Operating and Electrical | | Material Nr. (12NC) | 927908184020 |
| Power Consumption | 34.5 W | Numerator - Quantity Per Pack | 1 |
| Lamp Current (Nom) | 0.320 A | EAN/UPC - Product/Case | 046677220297 |
| | | Numerator - Packs per outer box | 10 |
| | | EAN/UPC - Case | 50046677220292 |

