



PL-L Long 4-Pin Base

PL-L 50W/830/4P/RS

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


Product data

General Information	
Cap-Base	2G11 [2G11]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	4,000 lumen
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	50.0 W
Lamp Current (Nom)	0.430 A
Voltage (Nom)	150 V

Voltage (Nom)	150 V
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	PL-L 50W/830/4P/RS
Order code	927908508321
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927908508321
Full product name	PL-L 50W/830/4P/RS
EAN/UPC - Case	50046677112672
EAN/UPC - Product/Case	046677112677

PL-L Long 4-Pin Base

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-L 50W/830/4P/RS	39.0 mm	18.0 mm	540 mm	565 mm	571.6 mm

Photometric data

Spectral Power Distribution Colour - PL-L 50W/830/4P/RS

