



# TUV PL-L

## TUV 55W PLL 25PK

TUV PL-L lamps are compact UVC (germicidal) lamps used in professional water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information		Mechanical and Housing	
Cap-Base	2G11 [2G11]	Lamp Current (Nom)	0.525 A
Useful Life (Nom)	9,000 hour(s)	Voltage (Nom)	105 V
Light Technical		Voltage (Nom)	105 V
Color Code	TUV	Bulb Shape	2xT16
Color Designation	- [Not Specified]	Approval and Application	
Depreciation at Useful Lifetime	20 %	Mercury (Hg) Content (Nom)	4.4 mg
Operating and Electrical			
Power Consumption	55 W		

# TUV PL-L

<b>UV</b>	
UV-C Radiation at 100 hr	18.7 W
<b>Product Data</b>	
Order product name	TUV PL-L 55W/4P HF 1CT/25
Full product name	TUV 55W PLL 25PK
Full product code	871150063379840
Order code	294645


Material Nr. (12NC)	927908704007
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500633798
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500633804

## Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 55W/4P HF 1CT/25	3/4 inch	1-1/2 inch	19-15/16 inch	20-7/8 inch	21-1/16 inch

## Photometric data



Spectral Power Distribution Colour - TUV PL-L 55W/4P HF 1CT/25

