



MASTER PL-L 4 Pin



MASTER PL-L 55W/830/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|----------------------------------|--------------------|
| Cap base | 2G11 |
| Flux measurement reference | Sphere |
| Light Technical | |
| Colour Code | 830 [CCT of 3000K] |
| Luminous Flux | 4,700 lm |
| Colour designation | Warm White (WW) |
| Chromaticity Coordinate X (Nom) | 0.44 |
| Chromaticity Coordinate Y (Nom) | 0.403 |
| Correlated Colour Temperature | 3000 K |
| Luminous efficacy (rated) (nom.) | 87 lm/W |
| Colour rendering index (CRI) | 82 |
| Operating and Electrical | |
| Power Consumption | 55.3 W |

| Lamp current (nom.) | 0.525 A |
|------------------------------------|-------------------------------|
| Controls and Dimming | |
| Dimmable | Yes |
| Approval and Application | |
| Energy Efficiency Class | G |
| Mercury (Hg) content (max.) | 2 mg |
| Mercury (Hg) content (nom.) | 2.0 mg |
| Energy consumption kWh/1,000 hours | 56 kWh |
| EPREL registration number | 423313 |
| Product Data | |
| Order product name | MASTER PL-L 55W/830/4P 1CT/25 |
| Full product name | MASTER PL-L 55W/830/4P 1CT/25 |
| Full EOC | 871150061541140 |
| Order code | 61541140 |

MASTER PL-L 4 Pin

| | |
|-----------------------------------|---------------|
| Material no. (12 NC) | 927908708370 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8711500615411 |
| Numerator – packs per outer box | 25 |


| | |
|----------------|---------------|
| EAN/UPC - Case | 8711500615541 |
|----------------|---------------|

Dimensional drawing



| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|-------------------------------|---------|----------|----------|---------|----------|
| MASTER PL-L 55W/830/4P 1CT/25 | 39.0 mm | 18.0 mm | 509.2 mm | 535 mm | 541.6 mm |

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 55W/830/4P 1CT/25

