



# PL-T Triple 4-Pin Base

## PL-T 26W/830/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


### Product data

| General Information                |                    |
|------------------------------------|--------------------|
| Cap-Base                           | GX24Q-3 [GX24q-3]  |
| Light Technical                    |                    |
| Color Code                         | 830 [CCT of 3000K] |
| Luminous Flux                      | 1,750 lm           |
| Color Designation                  | Warm White (WW)    |
| Correlated Color Temperature (Nom) | 3000 K             |
| Luminous Efficacy (rated) (Nom)    | 64.8 lm/W          |
| Color rendering index (CRI)        | >80                |
| Operating and Electrical           |                    |
| Power Consumption                  | 26 W               |
| Lamp Current (Nom)                 | 0.335 A            |
| Controls and Dimming               |                    |
| Dimmable                           | Yes                |

| Approval and Application        |                                    |
|---------------------------------|------------------------------------|
| Mercury (Hg) Content (Nom)      | 1.4 mg                             |
| Product Data                    |                                    |
| Order product name              | PL-T 26W/830/A/4P 1CT/5X10BOX ALTO |
| Full product name               | PL-T 26W/830/A/4P 1CT/5X10BOX ALTO |
| Order code                      | 458257                             |
| Material Nr. (12NC)             | 927910983050                       |
| Numerator - Quantity Per Pack   | 1                                  |
| EAN/UPC - Product/Case          | 046677268237                       |
| Numerator - Packs per outer box | 10                                 |
| EAN/UPC - Case                  | 50046677458251                     |


PL-T Triple 4-Pin Base

Dimensional drawing




| Product                            | D (max) | A (max) | B (max)  | C (max)  |
|------------------------------------|---------|---------|----------|----------|
| PL-T 26W/830/A/4P 1CT/5X10BOX ALTO | 41 mm   | 86.7 mm | 111.0 mm | 126.7 mm |

Photometric data




Spectral Power Distribution Colour - PL-T 26W/830/A/4P 1CT/5X10BOX ALTO

Lifetime




Lumen Maintenance Diagram - PL-T 26W/830/A/4P 1CT/5X10BOX ALTO



Life Expectancy Diagram - PL-T 26W/830/A/4P 1CT/5X10BOX ALTO

PL-T Triple 4-Pin Base

Lifetime



Life Expectancy Diagram - PL-T 26W/830/A/4P 1CT/5X10BOX ALTO

