



MASTER PL-T TOP 4 Pin

MASTER PL-T TOP 42W/830/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes. Amalgam controlled operation

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	GX24q-4	Power Consumption	42.0 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.320 A
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	3,000 lm	Approval and Application	
Color Designation	Warm White (WW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.44	Mercury (Hg) Content (Max)	1.4 mg
Chromaticity Coordinate Y (Nom)	0.403	Mercury (Hg) Content (Nom)	1.4 mg
Correlated Color Temperature (Nom)	3000 K	Energy Consumption kWh/1000 h	42 kWh
Luminous Efficacy (Rated) (Min)	80 lm/W	EPREL Registration Number	423331
Color rendering index (CRI)	80		

MASTER PL-T TOP 4 Pin

Product Data	
Order product name	MASTER PL-T TOP 42W/830/4P 1CT/5X10BOX
Full product name	MASTER PL-T TOP 42W/830/4P 1CT/5X10BOX
Full product code	871150061004170
Order code	927912283069
Material Nr. (12NC)	927912283069
Local order code	PLTT42W8304PA


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500610041
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500610072

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 42W/830/4P 1CT/ 5X10BOX	41 mm	120.7 mm	145.0 mm	160.7 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-T TOP 42W/830/4P 1CT/5X10BOX

MASTER PL-T TOP 4 Pin


Lifetime



Lumen Maintenance Diagram - MASTER PL-T TOP 42W/830/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 42W/830/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 42W/830/4P 1CT/5X10BOX

