



# MASTER PL-T TOP 4 Pin



## MASTER PL-T TOP 42W/840/4P 1CT/5X10CC

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes. Amalgam controlled operation

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	GX24Q-4 [GX24q-4]
Flux measurement reference	Sphere
Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	3,000 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (min.)	80 lm/W
Colour rendering index (CRI)	80


Operating and Electrical	
Power Consumption	42.0 W
Lamp current (nom.)	0.320 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	42 kWh
EPREL registration number	423332

MASTER PL-T TOP 4 Pin

Product Data	
Order product name	MASTER PL-T TOP 42W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-T TOP 42W/840/4P 1CT/5X10CC
Full EOC	871150061008970
Order code	61008970
Material no. (12 NC)	927912284069


SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500610089
Numerator – packs per outer box	50
EAN/UPC - Case	8711500610164

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 42W/840/4P 1CT/ 5X10BOX	41 mm	120.7 mm	145.0 mm	160.7 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-T TOP 42W/840/4P 1CT/5X10BOX

Lifetime




Lumen Maintenance Diagram - MASTER PL-T TOP 42W/840/4P 1CT/  
5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 42W/840/4P 1CT/5X10BOX

MASTER PL-T TOP 4 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-T TOP 42W/840/4P 1CT/5X10BOX

