



MASTER PL-T 4 Pin

MASTER PL-T 26W/840/4P 1CT/5X10BOX

MASTER PL-T is an efficient compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|------------------------------------|--------------------|
| Cap-Base | GX24Q-3 [GX24q-3] |
| Flux measurement reference | Sphere |
| | |
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 1,800 lm |
| Color Designation | Cool White (CW) |
| Chromaticity Coordinate X (Nom) | 0.38 |
| Chromaticity Coordinate Y (Nom) | 0.38 |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (Rated) (Min) | 66 lm/W |

| Color rendering index (CRI) | 80 |
|-----------------------------|---------|
| | |
| Operating and Electrical | |
| Power Consumption | 27.2 W |
| Lamp Current (Nom) | 0.300 A |
| | |
| Controls and Dimming | |
| Dimmable | Yes |
| | |
| Approval and Application | |
| Energy Efficiency Class | G |
| Mercury (Hg) Content (Max) | 1.4 mg |
| Mercury (Hg) Content (Nom) | 1.4 mg |

MASTER PL-T 4 Pin


| | |
|-------------------------------|--------|
| Energy Consumption kWh/1000 h | 28 kWh |
| EPREL Registration Number | 423348 |

Product Data

| | |
|--------------------|------------------------------------|
| Order product name | MASTER PL-T 26W/840/4P 1CT/5X10BOX |
| Full product name | MASTER PL-T 26W/840/4P 1CT/5X10BOX |
| Full product code | 871150061125370 |
| Order code | 927914684071 |


| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 927914684071 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500611253 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8711500611277 |

Dimensional drawing



| Product | D (max) | A (max) | B (max) | C (max) |
|------------------------------------|---------|---------|----------|----------|
| MASTER PL-T 26W/840/4P 1CT/5X10BOX | 41.0 mm | 86.7 mm | 111.0 mm | 126.7 mm |


Photometric data



Spectral Power Distribution Colour - MASTER PL-T 26W/840/4P 1CT/5X10BOX


MASTER PL-T 4 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-T 26W/840/4P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-T 26W/840/4P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-T 26W/840/4P 1CT/5X10BOX

