



MASTER PL-T 4 Pin



MASTER PL-T 32W/840/4P 1CT/5X10CC

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|----------------------------------|--------------------|
| Cap base | GX24q-3 |
| Flux measurement reference | Sphere |
| Light Technical | |
| Colour Code | 840 [CCT of 4000K] |
| Luminous Flux | 2,350 lm |
| Colour designation | Cool White (CW) |
| Chromaticity Coordinate X (Nom) | 0.38 |
| Chromaticity Coordinate Y (Nom) | 0.38 |
| Correlated Colour Temperature | 4000 K |
| Luminous efficacy (rated) (min.) | 75 lm/W |
| Colour rendering index (CRI) | 80 |
| Operating and Electrical | |
| Power Consumption | 32.0 W |


| Lamp current (nom.) | 0.320 A |
|------------------------------------|------------------------------------|
| Controls and Dimming | |
| Dimmable | Yes |
| Approval and Application | |
| Energy Efficiency Class | G |
| Mercury (Hg) content (max.) | 1.4 mg |
| Mercury (Hg) content (nom.) | 1.4 mg |
| Energy consumption kWh/1,000 hours | 32 kWh |
| EPREL registration number | 423351 |
| Product Data | |
| Order product name | MASTER PL-T 32W/840/4P 1CT/5X10BOX |
| Full product name | MASTER PL-T 32W/840/4P 1CT/5X10CC |
| Full EOC | 871150061131470 |
| Order code | 61131470 |

MASTER PL-T 4 Pin

| | |
|-----------------------------------|----------------|
| Material no. (12 NC) | 927914784071 |
| Local order code | 32PLT8404PINCS |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8711500611314 |


| | |
|---------------------------------|---------------|
| Numerator – packs per outer box | 50 |
| EAN/UPC – Case | 8711500611338 |

Dimensional drawing




| Product | D (max) | A (max) | B (max) | C (max) |
|------------------------------------|---------|---------|----------|----------|
| MASTER PL-T 32W/840/4P 1CT/5X10BOX | 41.0 mm | 98.7 mm | 123.0 mm | 138.7 mm |

Photometric data




Spectral Power Distribution Colour - MASTER PL-T 32W/840/4P 1CT/5X10BOX

Lifetime



Life Expectancy Diagram - MASTER PL-T 32W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T 32W/840/4P 1CT/5X10BOX

MASTER PL-T 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-T 32W/840/4P 1CT/5X10BOX

