



MASTER TL-D Super 80



MASTER TL-D Super 80 36W/840 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	15,000 h

Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	3,350 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	93 lm/W
Colour rendering index (CRI)	80

Operating and Electrical	
Power Consumption	36.8 W
Lamp current (nom.)	0.440 A

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb shape	T8

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (nom.)	1.7 mg
Energy consumption kWh/1,000 hours	37 kWh
EPREL registration number	423383

Product Data	
Order product name	MASTER TL-D Super 80 36W/840 1SL/25
Full product name	MASTER TL-D Super 80 36W/840 1SL/25
Full EOC	871150063201240
Order code	63201240
Material no. (12 NC)	927921084023
Local order code	36840


MASTER TL-D Super 80

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500632012
Numerator – packs per outer box	25


EAN/UPC - Case	8711500632029
----------------	---------------

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 36W/840 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm




Photometric data




Spectral Power Distribution Colour - MASTER TL-D Super 80 36W/840 1SL/25

Lifetime




Life Expectancy Diagram - MASTER TL-D Super 80 36W/840 1SL/25



Life Expectancy Diagram - MASTER TL-D Super 80 36W/840 1SL/25

MASTER TL-D Super 80

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Super 80 36W/840 1SL/25

