



MASTER TL-D Super 80

MASTER TL-D Super 80 36W/840 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	36.8 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.440 A
Life to 50% Failures (Nom)	15,000 hour(s)		
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	3,350 lm		
Color Designation	Cool White (CW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.38	Bulb Shape	T8
Chromaticity Coordinate Y (Nom)	0.38		
Correlated Color Temperature (Nom)	4000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	93 lm/W	Energy Efficiency Class	G
Color rendering index (CRI)	80	Mercury (Hg) Content (Nom)	1.7 mg
		Energy Consumption kWh/1000 h	37 kWh
		EPREL Registration Number	423383

MASTER TL-D Super 80

Product Data	
Order product name	MASTER TL-D Super 80 36W/840 1SL/25
Full product name	MASTER TL-D Super 80 36W/840 1SL/25
Full product code	871150063201240
Order code	927921084023
Material Nr. (12NC)	927921084023
Local order code	9279-210-84014


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500632012
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500632029

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 36W/840 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Super 80 36W/840 1SL/25

Lifetime




Life Expectancy Diagram - MASTER TL-D Super 80 36W/840 1SL/25



Life Expectancy Diagram - MASTER TL-D Super 80 36W/840 1SL/25

MASTER TL-D Super 80

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Super 80 36W/840 1SL/25

