



MASTER TL-D Eco



MASTER TL-D Eco 32W/865 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	15,000 h
Light Technical	
Colour Code	865 [CCT of 6500K]
Luminous Flux	2,550 lm
Colour designation	Cool Daylight
Chromaticity Coordinate X (Nom)	0.313
Chromaticity Coordinate Y (Nom)	0.337
Correlated Colour Temperature	6500 K
Luminous efficacy (rated) (nom.)	79 lm/W
Colour rendering index (CRI)	82
Operating and Electrical	
Power Consumption	32.4 W
Lamp current (nom.)	0.448 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	T8 [26 mm (T8)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (nom.)	1.7 mg
Energy consumption kWh/1,000 hours	33 kWh
EPREL registration number	423389
Product Data	
Order product name	MASTER TL-D Eco 32W/865 SLV/25
Full product name	MASTER TL-D Eco 32W/865 1SL/25
Full EOC	871150026464040
Order code	26464040
Material no. (12 NC)	927921186523
Local order code	32865TLDECO
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500264640

MASTER TL-D Eco


Numerator – packs per outer box	25
EAN/UPC - Case	8711500264657

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Eco 32W/865 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Eco 32W/865 SLV/25

Lifetime




Life Expectancy Diagram - MASTER TL-D Eco 32W/865 SLV/25



Life Expectancy Diagram - MASTER TL-D Eco 32W/865 SLV/25

MASTER TL-D Eco

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Eco 32W/865 SLV/25

