



# MASTER TL-D Super 80

## MASTER TL-D Super 80 23W/865 1SL/25

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	1,900 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	23.0 W
Lamp Current (Nom)	0.295 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	28 kWh
Product Data	
Order product name	MASTER TL-D Super 80 23W/865 1SL/25
Full product name	MASTER TL-D Super 80 23W/865 1SL/25
Full product code	872790091737600
Order code	927922586514
Material Nr. (12NC)	927922586514
Numerator - Quantity Per Pack	1

MASTER TL-D Super 80


EAN/UPC - Product/Case	8727900917376
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900917383

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 23W/865 1SL/25	28 mm	970.0 mm	977.1 mm	974.7 mm	984.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Super 80 23W/865 1SL/25

Lifetime



Life Expectancy Diagram - MASTER TL-D Super 80 23W/865 1SL/25



Life Expectancy Diagram - MASTER TL-D Super 80 23W/865 1SL/25

MASTER TL-D Super 80

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Super 80 23W/865 1SL/25

