



TL5 Essential HE Super 80

TL5 Essential 21W/840 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.
- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.


Product data

General Information		Controls and Dimming	
Cap-Base	G5	Dimmable	No
Light Technical		Mechanical and Housing	
Color Code	840 [CCT of 4000K]	Bulb Shape	T5
Luminous Flux	2,100 lm	Approval and Application	
Color Designation	Cool White (CW)	Mercury (Hg) Content (Nom)	2.0 mg
Correlated Color Temperature (Nom)	4000 K	Product Data	
Luminous Efficacy (rated) (Nom)	94 lm/W	Order product name	TL5 Essential 21W/840 1SL/40
Color rendering index (CRI)	82	Full product name	TL5 Essential 21W/840 1SL/40
Operating and Electrical		Full product code	871150057039055
Power Consumption	20.8 W	Order code	927926484058
Lamp Current (Nom)	0.170 A	Material Nr. (12NC)	927926484058
		Numerator - Quantity Per Pack	1

TL5 Essential HE Super 80


EAN/UPC - Product/Case	8711500570390
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500570406

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 21W/840 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

Photometric data



Spectral Power Distribution Colour - TL5 Essential 21W/840 1SL/40

