



# TL5 Essential HE Super 80

## TL5 Essential 28W/840 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

### Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.
- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.

### Product data

| General Information                |                    |
|------------------------------------|--------------------|
| Cap-Base                           | G5                 |
| Nominal lifetime                   | 15,000 hour(s)     |
| Light Technical                    |                    |
| Color Code                         | 840 [CCT of 4000K] |
| Luminous Flux                      | 2,900 lm           |
| Color Designation                  | Cool White (CW)    |
| Correlated Color Temperature (Nom) | 4000 K             |
| Luminous Efficacy (rated) (Nom)    | 94 lm/W            |
| Color rendering index (CRI)        | 82                 |
| Operating and Electrical           |                    |
| Power Consumption                  | 27.8 W             |
| Lamp Current (Nom)                 | 0.170 A            |


| Controls and Dimming          |                              |
|-------------------------------|------------------------------|
| Dimmable                      | No                           |
| Mechanical and Housing        |                              |
| Bulb Shape                    | T5                           |
| Approval and Application      |                              |
| Mercury (Hg) Content (Nom)    | 2.0 mg                       |
| Energy Consumption kWh/1000 h | 31 kWh                       |
| Product Data                  |                              |
| Order product name            | TL5 Essential 28W/840 1SL/40 |
| Full product name             | TL5 Essential 28W/840 1SL/40 |
| Full product code             | 871150057045155              |
| Order code                    | 927926784058                 |
| Material Nr. (12NC)           | 927926784058                 |

TL5 Essential HE Super 80

|                                 |               |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8711500570451 |
| Numerator - Packs per outer box | 40            |


|                |               |
|----------------|---------------|
| EAN/UPC - Case | 8711500570468 |
|----------------|---------------|

Dimensional drawing



| Product                         | D (max) | A (max)    | B (max)    | B (min)    | C (max)    |
|---------------------------------|---------|------------|------------|------------|------------|
| TL5 Essential 28W/840<br>1SL/40 | 17.0 mm | 1,149.0 mm | 1,156.1 mm | 1,153.7 mm | 1,163.2 mm |

Photometric data



Spectral Power Distribution Colour - TL5 Essential 28W/840 1SL/40

