



MASTER TL5 High Efficiency

MASTER TL5 HE 35W/835 SLV/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5 [G5]
Features	na [Not Applicable]
Light Technical	
Color Code	835 [CCT of 3500K]
Luminous Flux	3,650 lumen
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	35.5 W
Lamp Current (Nom)	0.175 A


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	38 kWh
Product Data	
Full product code	871150071006255
Order product name	MASTER TL5 HE 35W/835 SLV/40
Order code	927927083555
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40

MASTER TL5 High Efficiency

Material Nr. (12NC)	927927083555
Full product name	MASTER TL5 HE 35W/835 SLV/40
EAN/UPC - Case	8711500867674


EAN/UPC - Product/Case	8711500710062
------------------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 35W/835 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HE 35W/835 SLV/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HE 35W/835 SLV/40



Life Expectancy Diagram - MASTER TL5 HE 35W/835 SLV/40

MASTER TL5 High Efficiency

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE 35W/835 SLV/40

