



# MASTER TL5 High Output



## MASTER TL5 HO 49W/830 SLV/20

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Controls and Dimming	
Cap-Base	G5	Dimmable	Yes
Features	na [Not Applicable]		
Light Technical		Mechanical and Housing	
Color Code	830 [CCT of 3000K]	Bulb Shape	T5
Luminous Flux	4,900 lm		
Color Designation	Warm White (WW)	Approval and Application	
Correlated Color Temperature (Nom)	3000 K	Energy Efficiency Class	G
Luminous Efficacy (rated) (Nom)	89 lm/W	Mercury (Hg) Content (Nom)	1.2 mg
Color rendering index (CRI)	82	Energy Consumption kWh/1000 h	54 kWh
		EPREL Registration Number	423546
Operating and Electrical		Product Data	
Power Consumption	49.2 W	Order product name	MASTER TL5 HO 49W/830 SLV/20
Lamp Current (Nom)	0.255 A	Full product name	MASTER TL5 HO 49W/830 SLV/20
		Full product code	871150063954705

# MASTER TL5 High Output

Order code	927927583061
Material Nr. (12NC)	927927583061
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500639547


Numerator - Packs per outer box	20
EAN/UPC - Case	8711500264503

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 49W/830 SLV/20	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 49W/830 SLV/20

## Lifetime



Life Expectancy Diagram - MASTER TL5 HO 49W/830 SLV/20



Lumen Maintenance Diagram - MASTER TL5 HO 49W/830 SLV/20

# MASTER TL5 High Output

## Lifetime

Life Expectancy Diagram - MASTER TL5 HO 49W/830 SLV/20

