



MASTER TL5 高输出

MASTER TL5 HO 24W/830 SLV/40

直径 16 毫米的荧光灯

安全提示

· A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息	
底盖	G5 [G5]
功能	na [Not Applicable]
光通量测量参考	Sphere
灯技术	
颜色代码	830 [CCT of 3000K]
光通量	1,700 lm
颜色名称	暖白色 (WW)
色度坐标 X (标称)	0.44
色度坐标 Y (标称)	0.403
相关色温 (标称)	3000 K
光效 (额定) (标称)	76 lm/W
显色指数 (CRI)	82
操作和电气	
功耗	22.7 W
灯具电流 (标称)	0.295 A

控制和调光	
可调光	是
机械和外壳	
灯泡外形	T5 [16 毫米 (T5)]
审批和申请	
能效等级	G
汞 (Hg) 含量 (标称)	1.2 mg
能耗 kWh/1000 h	23 kWh
EPREL 注册号	423553
产品数据	
订单产品名称	MASTER TL5 HO 24W/830 SLV/40
完整的产品名称	MASTER TL5 HO 24W/830 SLV/40
完整产品代码	871150063958555
订购代码	927928083055
材料编号 (12NC)	927928083055
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500639585
计算器 - 每个外包装箱中的包数	40

MASTER TL5 高输出


EAN/UPC - 案例	8711500867759
--------------	---------------

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/830 SLV/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

光度数据




Spectral Power Distribution Colour - MASTER TL5 HO 24W/830 SLV/40

寿命



Life Expectancy Diagram - MASTER TL5 HO 24W/830 SLV/40



Life Expectancy Diagram - MASTER TL5 HO 24W/830 SLV/40

MASTER TL5 高输出

寿命

Lumen Maintenance Diagram - MASTER TL5 HO 24W/830 SLV/40

