



MASTER TL5 High Output

MASTER TL5 HO 24W/840 SLV/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G5 [G5]	Dimmable	Yes
Features	na [Not Applicable]		
Flux measurement reference	Sphere		
Light Technical		Mechanical and Housing	
Color Code	840 [CCT of 4000K]	Bulb Shape	T5 [16 mm (T5)]
Luminous Flux	1,700 lm		
Color Designation	Cool White (CW)	Approval and Application	
Chromaticity Coordinate X (Nom)	0.38	Energy Efficiency Class	G
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Nom)	1.2 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	23 kWh
Luminous Efficacy (rated) (Nom)	76 lm/W	EPREL Registration Number	423555
Color rendering index (CRI)	82		
Operating and Electrical		Product Data	
Power Consumption	22.7 W	Order product name	MASTER TL5 HO 24W/840 SLV/40
Lamp Current (Nom)	0.295 A	Full product name	MASTER TL5 HO 24W/840 SLV/40
		Full product code	871150063960855
		Order code	927928084055
		Material Nr. (12NC)	927928084055
		Numerator - Quantity Per Pack	1

MASTER TL5 High Output


EAN/UPC - Product/Case	8711500639608
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500867841

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/840 SLV/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 24W/840 SLV/40

Lifetime




Life Expectancy Diagram - MASTER TL5 HO 24W/840 SLV/40



Life Expectancy Diagram - MASTER TL5 HO 24W/840 SLV/40

MASTER TL5 High Output

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 24W/840 SLV/40

