



MASTER TL5 High Output

MASTER TL5 HO 54W/830 SLV/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5 [G5]
Features	na [Not Applicable]
Flux measurement reference	Sphere
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	4,500 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	54.4 W
Lamp Current (Nom)	0.455 A


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	55 kWh
EPREL Registration Number	423562
Product Data	
Order product name	MASTER TL5 HO 54W/830 SLV/40
Full product name	MASTER TL5 HO 54W/830 SLV/40
Full product code	871150064316255
Local code description	TL554W830HO
Order code	927929083055
Material Nr. (12NC)	927929083055

MASTER TL5 High Output

Local order code	TL554W830HO
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500643162
Numerator - Packs per outer box	40


EAN/UPC - Case	8711500868824
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 54W/830 SLV/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 54W/830 SLV/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HO 54W/830 SLV/40



Life Expectancy Diagram - MASTER TL5 HO 54W/830 SLV/40

MASTER TL5 High Output

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 54W/830 SLV/40

