



# MASTER TL5 High Output



## MASTER TL5 HO 54W/840 UNP/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G5 [G5]
Features	na [Not Applicable]
Flux measurement reference	Sphere
Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	4,500 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	83 lm/W
Colour rendering index (CRI)	80
Operating and Electrical	
Power Consumption	54.4 W
Lamp current (nom.)	0.455 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	T5 [16 mm (T5)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (nom.)	1.2 mg
Energy consumption kWh/1,000 hours	55 kWh
EPREL registration number	423563
Product Data	
Order product name	MASTER TL5 HO 54W/840 UNP/40
Full product name	MASTER TL5 HO 54W/840 UNP/40
Full EOC	871150063740655
Order code	63740655
Material no. (12 NC)	927929084018
SAP numerator – quantity per pack	1

MASTER TL5 High Output


EAN/UPC — Product/Case	8711500637406
Numerator – packs per outer box	40
EAN/UPC - Case	8711500637413

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 54W/840 UNP/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 54W/840 UNP/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HO 54W/840 UNP/40



Life Expectancy Diagram - MASTER TL5 HO 54W/840 UNP/40

# MASTER TL5 High Output

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 54W/840 UNP/40

