



T5 High Output

F54T5/TL830/HO/XXL 40 PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.


Product data

General Information	
Cap-Base	G5 [G5]
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	5,000 lumen
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	54.1 W
Lamp Current (Nom)	0.455 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	57 kWh
Product Data	
Order product name	F54T5/TL830/HO/XXL 40 PK
Order code	927929283020
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927929283020
Full product name	F54T5/TL830/HO/XXL 40 PK
EAN/UPC - Case	50046677453966
EAN/UPC - Product/Case	046677453961


T5 High Output

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F54T5/TL830/HO/XXL 40 PK	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - F54T5/TL830/HO/XXL 40 PK

Lifetime





Life Expectancy Diagram - F54T5/TL830/HO/XXL 40 PK



Life Expectancy Diagram - F54T5/TL830/HO/XXL 40 PK

T5 High Output

Lifetime



Life Expectancy Diagram - F54T5/TL830/HO/XXL 40 PK

Lumen Maintenance Diagram - F54T5/TL830/HO/XXL 40 PK

