



MASTER TL5 High Output Xtra

MASTER TL5 HO Xtra 54W/830 SLV/20

This TL5 lamp (tube diameter 16 mm) combines the advantages of a TL5 High Output lamp (TL5 HO lamps are optimized for installations requiring high light output and offer excellent lumen maintenance and color rendering) with a long and reliable lifetime. This results in extra-low maintenance costs and saves on expensive spot replacement. Main applications are places where lamp replacement costs and/or costs of disruption are high.

Warnings and Safety

- Philips HF Xtreme gear ensures longest lifetime.
- To achieve lifetimes as published for 100% operation, dimming below 30% should not be applied.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	G5 [G5]	Power Consumption	54.1 W
		Lamp Current (Nom)	0.455 A
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	5,000 lm		
Color Designation	Warm White (WW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	3000 K	Bulb Shape	T5 [16 mm (T5)]
Luminous Efficacy (rated) (Nom)	83 lm/W		
Color rendering index (CRI)	82	Approval and Application	
		Mercury (Hg) Content (Nom)	3.0 mg

MASTER TL5 High Output Xtra

Energy Consumption kWh/1000 h	57 kWh
Product Data	
Order product name	MASTER TL5 HO Xtra 54W/830 SLV/20
Full product name	MASTER TL5 HO Xtra 54W/830 SLV/20
Full product code	871150026323005
Order code	927929283026

Material Nr. (12NC)	927929283026
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500263230
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500263247

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Xtra 54W/830 SLV/20	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER TL5 HO Xtra 54W/830 SLV/20

Lifetime




Life Expectancy Diagram - MASTER TL5 HO Xtra 54W/830 SLV/20

Life Expectancy Diagram - MASTER TL5 HO Xtra 54W/830 SLV/20

MASTER TL5 High Output Xtra

Lifetime



Life Expectancy Diagram - MASTER TL5 HO Xtra 54W/830 SLV/20

Lumen Maintenance Diagram - MASTER TL5 HO Xtra 54W/830 SLV/20

