

MASTER TL5 High Output Xtra

MASTER TL5 HO Xtra 54W/840 SLV/20

Low-pressure high-output mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- Philips HF Xtreme gear ensures longest lifetime.
- To achieve lifetimes as published for 100% operation, dimming below 30% should not be applied.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5 [G5]
Flux measurement reference	Sphere
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	4,500 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	53.8 W

Lamp Current (Nom)	0.455 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	3 mg
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	54 kWh
EPREL Registration Number	423567
Product Data	
Order product name	MASTER TL5 HO Xtra 54W/840 SLV/20

MASTER TL5 High Output Xtra

Full product name	MASTER TL5 HO Xtra 54W/840 SLV/20
Full product code	871150026352005
Local code description	TL554W840 XTRA
Order code	927929284026
Material Nr. (12NC)	927929284026
Local order code	TL554W840 XTRA

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500263520
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500263544

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Xtra 54W/840 SLV/20	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO Xtra 54W/840 SLV/20

Lifetime




Life Expectancy Diagram - MASTER TL5 HO Xtra 54W/840 SLV/20



Life Expectancy Diagram - MASTER TL5 HO Xtra 54W/840 SLV/20

MASTER TL5 High Output Xtra

Lifetime



Life Expectancy Diagram - MASTER TL5 HO Xtra 54W/840 SLV/20

Lumen Maintenance Diagram - MASTER TL5 HO Xtra 54W/840 SLV/20

