



T5 High Output

F54T5/TL850/HO/XXL 40 PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.


Product data

| General Information | |
|------------------------------------|--------------------|
| Cap-Base | G5 [G5] |
| Light Technical | |
| Color Code | 850 [CCT of 5000K] |
| Luminous Flux | 4,800 lumen |
| Color Designation | Daylight |
| Correlated Color Temperature (Nom) | 5000 K |
| Luminous Efficacy (rated) (Nom) | 80 lm/W |
| Color rendering index (CRI) | 82 |
| Operating and Electrical | |
| Power Consumption | 54 W |
| Lamp Current (Nom) | 0.455 A |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|--------------------------|
| Bulb Shape | T5 [16 mm (T5)] |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 3.0 mg |
| Energy Consumption kWh/1000 h | 57 kWh |
| Product Data | |
| Order product name | F54T5/TL850/HO/XXL 40 PK |
| Order code | 927929285020 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 40 |
| Material Nr. (12NC) | 927929285020 |
| Full product name | F54T5/TL850/HO/XXL 40 PK |
| EAN/UPC - Case | 50046677453980 |
| EAN/UPC - Product/Case | 046677453985 |

T5 High Output

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|--------------------------|---------|------------|------------|------------|------------|
| F54T5/TL850/HO/XXL 40 PK | 17 mm | 1,149.0 mm | 1,156.1 mm | 1,153.7 mm | 1,163.2 mm |

