



MASTER PL-L Polar 4 Pin

MASTER PL-L POLAR 24W/830/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes linked by a bridge. 4-pin base without gear

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	2G11 [2G11]
Life to 50% failures (nom.)	15,000 h
Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	1,800 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	75 lm/W
Colour rendering index (CRI)	82
Operating and Electrical	
Power Consumption	24.0 W


Lamp current (nom.)	0.350 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) content (nom.)	2.0 mg
Energy consumption kWh/1,000 hours	26 kWh
Product Data	
Order product name	MASTER PL-L Polar 24W/830/4P 1CT/25
Full product name	MASTER PL-L POLAR 24W/830/4P 1CT/25
Full EOC	871150026154040
Local code description	24PLL830OUT

MASTER PL-L Polar 4 Pin

Order code	26154040
Material no. (12 NC)	927930583070
Local order code	24PLL830OUT
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500261540


Numerator – packs per outer box	25
EAN/UPC – Case	8711500261557

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L Polar 24W/830/4P 1CT/25	39.0 mm	18.0 mm	290 mm	315 mm	321.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L Polar 24W/830/4P 1CT/25

