



# MASTER PL-L Polar 4 Pin



## MASTER PL-L POLAR 55W/840/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes linked by a bridge. 4-pin base without gear

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	2G11	Power Consumption	55.3 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.550 A
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	4,650 lm	Approval and Application	
Color Designation	Cool White (CW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.38	Mercury (Hg) Content (Max)	2 mg
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Nom)	2.0 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	56 kWh
Luminous Efficacy (rated) (Nom)	87 lm/W	EPREL Registration Number	423577
Color rendering index (CRI)	80		

# MASTER PL-L Polar 4 Pin

Product Data	
Order product name	MASTER PL-L Polar 55W/840/4P 1CT/25
Full product name	MASTER PL-L POLAR 55W/840/4P 1CT/25
Full product code	871150026164940
Order code	26164940
Material Nr. (12NC)	927931584070


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500261649
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500261656

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L Polar 55W/840/4P 1CT/25	39.0 mm	18.0 mm	510 mm	535 mm	541.6 mm

## Photometric data



Spectral Power Distribution Colour - MASTER PL-L Polar 55W/840/4P 1CT/25

