



MASTER PL-S 2 Pin



MASTER PL-S 9W/827/2P 1CT/5X10BOX

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Luminous efficacy (rated) (nom.)		67 lm/W
Cap base	G23	Colour rendering index (CRI)		82
Flux measurement reference	Sphere	Operating and Electrical		
Life to 50% failures (nom.)	10,000 h	Power Consumption	8.8 W	
Light Technical		Lamp current (nom.)	0.170 A	
Colour Code	827 [CCT of 2700K]	Controls and Dimming		
Luminous Flux	600 lm	Dimmable	No	
Colour designation	Incandescent White	Approval and Application		
Chromaticity Coordinate X (Nom)	0.463	Energy Efficiency Class	G	
Chromaticity Coordinate Y (Nom)	0.42			
Correlated Colour Temperature	2700 K			

MASTER PL-S 2 Pin


Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	9 kWh
EPREL registration number	423588

Product Data

Order product name	MASTER PL-S 9W/827/2P 1CT/5X10BOX
Full product name	MASTER PL-S 9W/827/2P 1CT/5X10BOX
Full EOC	871150026079670


Order code	26079670
Material no. (12 NC)	927936082711
Local order code	9PLS8272PINB
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500260796
Numerator – packs per outer box	50
EAN/UPC – Case	8711500260819

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 9W/827/2P 1CT/5X10BOX	28 mm	13 mm	129 mm	145 mm	167 mm



Photometric data



Spectral Power Distribution Colour - MASTER PL-S 9W/827/2P 1CT/5X10BOX


MASTER PL-S 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-S 9W/827/2P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-S 9W/827/2P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-S 9W/827/2P 1CT/5X10BOX

