

PL-S consumer products



PL-S 9W/827/2P 1PP/10

The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base. Not suitable for dimming

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G23
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	600 lm
Color Designation	Incandescent White
Chromaticity Coordinate X (Nom)	0.463
Chromaticity Coordinate Y (Nom)	0.42
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	8.8 W


Lamp Current (Nom)	0.170 A
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	9 kWh
EPREL Registration Number	423589
Product Data	
Order product name	PL-S 9W/827/2P 1PP/10
Full product name	PL-S 9W/827/2P 1PP/10
Full product code	871150070311825
Order code	927936082767
Material Nr. (12NC)	927936082767

PL-S consumer products

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500703118
Numerator - Packs per outer box	10


EAN/UPC - Case	8711500897381
----------------	---------------

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-S 9W/827/2P 1PP/10	28 mm	13 mm	129 mm	145 mm	167 mm

Photometric data




Spectral Power Distribution Colour - PL-S 9W/827/2P 1PP/10

Lifetime




Life Expectancy Diagram - PL-S 9W/827/2P 1PP/10



Life Expectancy Diagram - PL-S 9W/827/2P 1PP/10

PL-S consumer products

Lifetime



Lumen Maintenance Diagram - PL-S 9W/827/2P 1PP/10

