



PL-S consumer products

PL-S 11W/827/2P 1BL/10

The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base. Not suitable for dimming

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G23 [G23]
Life to 50% Failures (Nom)	10,000 hour(s)

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	900 lm
Color Designation	Incandescent White
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	11.6 W
Lamp Current (Nom)	0.155 A


Controls and Dimming	
Dimmable	No

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	14 kWh

Product Data	
Order product name	PL-S 11W/827/2P 1BL/10
Full product name	PL-S 11W/827/2P 1BL/10
Full product code	871150063358325
Order code	927936482715
Material Nr. (12NC)	927936482715
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500633583
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500633590


PL-S consumer products

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-S 11W/827/2P 1BL/10	28 mm	13 mm	198 mm	214 mm	235.8 mm

Photometric data



Spectral Power Distribution Colour - PL-S 11W/827/2P 1BL/10

Lifetime



Life Expectancy Diagram - PL-S 11W/827/2P 1BL/10

Life Expectancy Diagram - PL-S 11W/827/2P 1BL/10

PL-S consumer products

Lifetime



Lumen Maintenance Diagram - PL-S 11W/827/2P 1BL/10

