



# MASTER PL-S 2 Pin



## MASTER PL-S 11W/840/2P 1CT/5X10BOX

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Luminous efficacy (rated) (nom.)	
Cap base	G23 [G23]	77 lm/W	
Flux measurement reference	Sphere	Colour rendering index (CRI)	
Life to 50% failures (nom.)	10,000 h	80	
Light Technical		Operating and Electrical	
Colour Code	840 [CCT of 4000K]	Power Consumption	11.9 W
Luminous Flux	900 lm	Lamp current (nom.)	0.155 A
Colour designation	Cool White (CW)	Controls and Dimming	
Chromaticity Coordinate X (Nom)	0.38	Dimmable	No
Chromaticity Coordinate Y (Nom)	0.38	Approval and Application	
Correlated Colour Temperature	4000 K	Energy Efficiency Class	G

MASTER PL-S 2 Pin


Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	12 kWh
EPREL registration number	423598

Product Data

Order product name	MASTER PL-S 11W/840/2P 1CT/5X10BOX
Full product name	MASTER PL-S 11W/840/2P 1CT/5X10BOX
Full EOC	871150026109070


Order code	26109070
Material no. (12 NC)	927936484011
Local order code	11PLS8402PINB
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500261090
Numerator – packs per outer box	50
EAN/UPC – Case	8711500261113

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 11W/840/2P 1CT/ 5X10BOX	28 mm	13 mm	198 mm	214 mm	235.8 mm



Photometric data



Spectral Power Distribution Colour – MASTER PL-S 11W/840/2P 1CT/5X10BOX

MASTER PL-S 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-S 11W/840/2P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-S 11W/840/2P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-S 11W/840/2P 1CT/5X10BOX

