



MASTER PL-S 4 Pin



MASTER PL-S 11W/840/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	2G7 [2G7]
Flux measurement reference	Sphere
Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	880 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	82 lm/W
Colour rendering index (CRI)	80
Operating and Electrical	
Power Consumption	11.9 W


Lamp current (nom.)	0.160 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	12 kWh
EPREL registration number	423601
Product Data	
Order product name	MASTER PL-S 11W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-S 11W/840/4P 1CT/5X10BOX
Full EOC	871150026122970
Order code	26122970

MASTER PL-S 4 Pin

Material no. (12 NC)	927936684011
Local order code	11PLS8404PINB
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500261229


Numerator – packs per outer box	50
EAN/UPC – Case	8711500261243

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 11W/840/4P 1CT/ 5X10BOX	28 mm	13 mm	196 mm	214 mm	219.9 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-S 11W/840/4P 1CT/5X10BOX

Lifetime




Life Expectancy Diagram - MASTER PL-S 11W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-S 11W/840/4P 1CT/5X10BOX

MASTER PL-S 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-S 11W/840/4P 1CT/5X10BOX

