



PL-Q 4 Pin



PL-Q 38W/835/4P 1CT/10BOX

Compact fluorescent lamps with a quadrant-like shape

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap base	GR10Q [GR10q]
Flux measurement reference	Sphere
Light Technical	
Colour Code	835 [CCT of 3500K]
Luminous Flux	2,750 lm
Colour designation	White (WH)
Chromaticity Coordinate X (Nom)	0.409
Chromaticity Coordinate Y (Nom)	0.394
Correlated Colour Temperature	3500 K
Luminous efficacy (rated) (nom.)	75 lm/W
Colour rendering index (CRI)	81
Operating and Electrical	
Power Consumption	38.4 W
Lamp current (nom.)	0.430 A

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	3 mg
Mercury (Hg) content (nom.)	4 mg
Energy consumption kWh/1,000 hours	39 kWh
EPREL registration number	423616
Product Data	
Order product name	PL-Q 38W/835/4P 1CT/10BOX
Full product name	PL-Q 38W/835/4P 1CT/10BOX
Full EOC	871150027173025
Order code	27173025
Material no. (12 NC)	927939483540
Local order code	38PLQ8354PIN
SAP numerator – quantity per pack	1

PL-Q 4 Pin


EAN/UPC — Product/Case	8711500271730
Numerator – packs per outer box	10
EAN/UPC - Case	8711500271655

Dimensional drawing





Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 38W/835/4P 1CT/10BOX	46.5 mm	18.9 mm	33 mm	203 mm	76 mm	41 mm	200 mm

Photometric data



Spectral Power Distribution Colour - PL-Q 38W/835/4P 1CT/10BOX

Lifetime



Lumen Maintenance Diagram - PL-Q 38W/835/4P 1CT/10BOX

Life Expectancy Diagram - PL-Q 38W/835/4P 1CT/10BOX

PL-Q 4 Pin

Lifetime



Life Expectancy Diagram - PL-Q 38W/835/4P 1CT/10BOX

