



MASTER TL-D Xtra

MASTER TL-D Xtra 18W/840 1SL/25

Low-pressure mercury discharge lamp with a tubular 26mm envelope

Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% failures (nom.)	36,000 h		
Light Technical		Mechanical and Housing	
Colour Code	840 [CCT of 4000K]	Bulb shape	T8 [26 mm (T8)]
Luminous Flux	1,350 lm		
Colour designation	Cool White (CW)	Approval and Application	
Correlated Colour Temperature	4000 K	Mercury (Hg) content (nom.)	3.0 mg
Luminous efficacy (rated) (nom.)	76 lm/W	Energy consumption kWh/1,000 hours	22 kWh
Colour rendering index (CRI)	>80		
Operating and Electrical		Product Data	
Power Consumption	17.7 W	Order product name	MASTER TL-D Xtra 18W/840 SLV/25
Lamp current (nom.)	0.370 A	Full product name	MASTER TL-D Xtra 18W/840 1SL/25
		Full EOC	871150055862640
		Order code	55862640
		Material no. (12 NC)	927980484014
		Local order code	18840XTRA
		SAP numerator – quantity per pack	1

MASTER TL-D Xtra


EAN/UPC — Product/Case	8711500558626
Numerator – packs per outer box	25
EAN/UPC - Case	8711500558657

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtra 18W/840 SLV/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Xtra 18W/840 SLV/25

Lifetime




Life Expectancy Diagram - MASTER TL-D Xtra 18W/840 SLV/25



Life Expectancy Diagram - MASTER TL-D Xtra 18W/840 SLV/25

MASTER TL-D Xtra

Lifetime



Life Expectancy Diagram - MASTER TL-D Xtra 18W/840 SLV/25

Lumen Maintenance Diagram - MASTER TL-D Xtra 18W/840 SLV/25

