

MASTER TL-D Super 80

TL-D 18W/830 1SL/25

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	13,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	830 [CCT of 3000K]	Bulb Shape	T8 [26 mm (T8)]
Color Designation	Warm White (WW)		
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	75 lm/W	Mercury (Hg) Content (Nom)	2.0 mg
Color rendering index (CRI)	83		
Operating and Electrical		Product Data	
Power Consumption	18 W	Order product name	TL-D 18W/830 1SL/25
Lamp Current (Nom)	0.360 A	Full product name	TL-D 18W/830 1SL/25
Voltage (Nom)	59 V	Full product code	871829125412600
Voltage (Nom)	59 V	Order code	927981183024
		Material Nr. (12NC)	927981183024
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718291254126

MASTER TL-D Super 80


Numerator - Packs per outer box	25
EAN/UPC - Case	8718291254133

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/830 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data




Spectral Power Distribution Colour - TL-D 18W/830 1SL/25

Lifetime



Life Expectancy Diagram - TL-D 18W/830 1SL/25



Life Expectancy Diagram - TL-D 18W/830 1SL/25

MASTER TL-D Super 80

Lifetime

Lumen Maintenance Diagram - TL-D 18W/830 1SL/25

