



MASTER TL-D Xtreme

MASTER TL-D Xtreme 36W/840 SLV

Low-pressure mercury discharge lamp with a tubular 26mm envelope

Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	0.430 A	
Flux measurement reference	Sphere	Controls and Dimming	
Life to 50% Failures (Nom)	47,000 hour(s)	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	840 [CCT of 4000K]	Bulb Shape	T8
Luminous Flux	3,200 lm	Approval and Application	
Color Designation	Cool White (CW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.38	Mercury (Hg) Content (Max)	3 mg
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Nom)	3.0 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	37 kWh
Luminous Efficacy (rated) (Nom)	90 lm/W	EPREL Registration Number	423630
Color rendering index (CRI)	82	Product Data	
Operating and Electrical		Order product name	MASTER TL-D Xtreme 36W/840 SLV
Power Consumption	36.4 W	Full product name	MASTER TL-D Xtreme 36W/840 SLV

MASTER TL-D Xtreme

Full product code	871150055868840
Order code	927982384014
Material Nr. (12NC)	927982384014
Local order code	TLD36W840XTREM
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500558688
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500558695

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtreme 36W/840 SLV	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Xtreme 36W/840 SLV

Lifetime





Life Expectancy Diagram - MASTER TL-D Xtreme 36W/840 SLV



Life Expectancy Diagram - MASTER TL-D Xtreme 36W/840 SLV

MASTER TL-D Xtreme

Lifetime



Life Expectancy Diagram - MASTER TL-D Xtreme 36W/840 SLV

Lumen Maintenance Diagram - MASTER TL-D Xtreme 36W/840 SLV

