



MASTER TL-D Xtra (特级型)

MASTER TL-D Xtra 36W/830 SLV/25

低压汞放电灯，配备管状 26 毫米的封装。

安全提示

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	G13 [Medium Bi-Pin Fluorescent]
50% 故障条件下的使用寿命 (标称)	36,000 小时
灯技术	
颜色代码	830 [CCT of 3000K]
光通量	3,350 lm
颜色名称	暖白色 (WW)
相关色温 (标称)	3000 K
光效 (额定)(标称)	93 lm/W
显色指数 (CRI)	>80
操作和电气	
功耗	37.0 W
灯具电流 (标称)	0.435 A


控制和调光	
可调光	是
机械和外壳	
灯泡外形	T8 [26 毫米 (T8)]
审批和申请	
汞 (Hg) 含量 (标称)	3.0 mg
能耗 kWh/1000 h	43 kWh
产品数据	
订单产品名称	MASTER TL-D Xtra 36W/830 SLV/25
完整的产品名称	MASTER TL-D Xtra 36W/830 SLV/25
完整产品代码	871150055871840
订购代码	927982483014
材料编号 (12NC)	927982483014

MASTER TL-D Xtra (特级型)

计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500558718
计算器 - 每个外包装箱中的包数	25


EAN/UPC - 案例	8711500558732
--------------	---------------

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtra 36W/830 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

光度数据




Spectral Power Distribution Colour - MASTER TL-D Xtra 36W/830 SLV/25

寿命




Life Expectancy Diagram - MASTER TL-D Xtra 36W/830 SLV/25



Life Expectancy Diagram - MASTER TL-D Xtra 36W/830 SLV/25

MASTER TL-D Xtra (特级型)

寿命



Life Expectancy Diagram - MASTER TL-D Xtra 36W/830 SLV/25



Lumen Maintenance Diagram - MASTER TL-D Xtra 36W/830 SLV/25

