



MASTER TL-D Xtra

MASTER TL-D Xtra 36W/865 1SL

Low-pressure mercury discharge lamp with a tubular 26mm envelope

Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% failures (nom.)	36,000 h		
Light Technical		Mechanical and Housing	
Colour Code	865 [CCT of 6500K]	Bulb shape	T8 [26 mm (T8)]
Luminous Flux	3,200 lm	Approval and Application	
Colour designation	Cool Daylight	Mercury (Hg) content (nom.)	3.0 mg
Correlated Colour Temperature	6500 K	Energy consumption kWh/1,000 hours	44 kWh
Luminous efficacy (rated) (nom.)	87 lm/W	Product Data	
Colour rendering index (CRI)	>80	Order product name	MASTER TL-D Xtra 36W/865 SLV
Operating and Electrical		Full product name	MASTER TL-D Xtra 36W/865 1SL
Power Consumption	37.0 W	Full EOC	871150089283640
Lamp current (nom.)	0.435 A	Order code	89283640
		Material no. (12 NC)	927982486514
		Local order code	36865XTRA
		SAP numerator – quantity per pack	1

MASTER TL-D Xtra


EAN/UPC — Product/Case	8711500892836
Numerator – packs per outer box	25
EAN/UPC - Case	8711500892843

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtra 36W/865 SLV	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Xtra 36W/865 SLV

Lifetime




Life Expectancy Diagram - MASTER TL-D Xtra 36W/865 SLV



Life Expectancy Diagram - MASTER TL-D Xtra 36W/865 SLV

MASTER TL-D Xtra

Lifetime



Life Expectancy Diagram - MASTER TL-D Xtra 36W/865 SLV

Lumen Maintenance Diagram - MASTER TL-D Xtra 36W/865 SLV

