



MASTER TL-D Xtra

MASTER TL-D Xtra 58W/840 SLV/25

Low-pressure mercury discharge lamp with a tubular 26mm envelope

Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	36,000 h
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	5,200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	91 lm/W
Color rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	58.5 W
Lamp Current (Nom)	0.665 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	68 kWh
Product Data	
Order product name	MASTER TL-D Xtra 58W/840 SLV/25
Full product name	MASTER TL-D Xtra 58W/840 SLV/25
Full product code	871150055890940
Order code	927983484014
Material Nr. (12NC)	927983484014
Local order code	TLD58W840XTRA
Numerator - Quantity Per Pack	1

MASTER TL-D Xtra


EAN/UPC - Product/Case	8711500558909
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500558916

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtra 58W/840 SLV/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Xtra 58W/840 SLV/25

Lifetime




Life Expectancy Diagram - MASTER TL-D Xtra 58W/840 SLV/25



Life Expectancy Diagram - MASTER TL-D Xtra 58W/840 SLV/25

MASTER TL-D Xtra

Lifetime



Life Expectancy Diagram - MASTER TL-D Xtra 58W/840 SLV/25

Lumen Maintenance Diagram - MASTER TL-D Xtra 58W/840 SLV/25

